## Modalità di funzionamento

È un dispositivo di potenza che, generando in sequenza due impulsi distinti, consente a un cilindro a doppio effetto o a un analogo impianto pneumatico di effettuare la fase di andata e ritorno.

Diversamente da una normale valvola a 5 vie, che ne ha due ("14" e "12"), il flip-flop presenta un unico punto di comando, a partire dal quale vengono generati gli impulsi relativi ad ambedue le fasi del ciclo del cilindro. Per il funzionamento del flip-flop è necessario dunque inviare un segnale di comando, pneumatico o elettrico, al punto X; questo segnale genera un solo impulso.

Il flip-flop non consente la ripetitività dell'impulso generato, ovvero non è possibile, perdurando il segnale di comando, produrre nuovi impulsi dopo il primo (a questo scopo è necessario inviare un nuovo segnale). Affinché il cilindro effettui un ciclo completo di andata e ritorno è pertanto necessario inviare al flip-flop due distinti segnali di comando.

In caso di blocco del flip-flop dovuto a un'interruzione di pressione è possibile ripristinarne la normale funzionalità tramite i due riarmi manuali.

## Esistono due tipi di flip-flop:

cod. **10.035.4** L'impulso è attivato da un segnale pneumatico inviato al punto **X**. La pressione del segnale di comando può essere differente rispetto a quella utilizzata per azionare il cilindro.

cod. 10.018.3 L'impulso è attivato da un comando elettrico.

### Materiali

Corpo: alluminio 11S

Molle: INOX Guarnizioni: NBR

Spole: alluminio nichelato Parti interne: ottone OT58

I prodotti di seguito indicati sono venduti senza bobine, da acquistarsi separatamente (vedi pag. 372).

The following listed products are sold without coils, which are bought separately (refer to page 372).

Attacchi  Ports		G1/4"
Pressione di esercizio  Working pressure		3 10 bar 0.3 1 MPa
Pressione di azionamento pneumatico (X)  Pneumatic actuating pressure (X)		2 10 bar 0.2 1 MPa
Temperatura di esercizio  Temperature range		max +60°C
Fluido Fluid	Aria filtrata 50 $\mu$ con o senza lubrificazione 50 $\mu$ filtered, lubricated or non lubricated air	

# Valve operation

This is a high-flow device which, by applying a pilot pressure either pneumatic or electrical to point **X**, will, for example, extend and retract a double acting cylinder.

The "flip-flop" valve requires two pilot signals for a complete cycle: one momentary signal to extend the cylinder stroke and one momentary signal to retract. A maintained pilot signal will generate one half of the cycle. The valve will stay in this position until the signal is exhausted and then applied again.

In the event of pilot pressure failure or system maintenance a manual override facility is provided.

#### Two types of flip-flop valves are available:

code **10.035.4** The valve is actuated by applying a pneumatic signal to point **X**. The signal pressure can be different to the pressure at port **1**.


code 10.018.3 The valve is actuated by an electrical signal.

#### Materials

Body: aluminium 11S Springs: stainless steel


Seals: NBR


Spools: nickel plated aluminium Internal parts: brass 0T58



a comando pneumatico pneumatically piloted










a comando elettrico solenoid piloted









# KOMPAUT s.r.l.

VIA TONALE, 295/305
21050 MARNATE (VA)
TEL.: 0331/369.249
E-MAIL: info@kompaut.com

www.kompaut.com